

PRH 010-M | PRH 020-M | PRH 030-M MINI-RADIANT HEATERS 10–30 W

The PRH Mini series of radiant heaters consists of three versions with heating performance ratings of 10, 20 and 30 Watts. The new mini-heaters by Pfannenberg are particularly suitable for use in small housings or for the heating of isolated spots in sensitive areas.



PRODUCT	PRH 010-M	PRH 020-M	PRH 030-M	
ARTICLE NO.	17000105317	17000205317	17000305317	Unit

DATA

Heating performance (Ta = +20 °C)	10	20	30	W	
Rated voltage ±10 %	AC 50 60 Hz			V	
	230				
Functional range	110–250 V AC 50 60 Hz			°C	
Max. starting current	1.0	1.1	1.2		A
Max. surface temperature	95	115	140		°C
Operating temperature	–40 ... +70				
System of protection for intended purpose of use	IP 54				
Protection class	II				
Device construction	aluminium profile, black anodised				
Type of mounting	snap fastening for 35 mm profile bars according to EN 60715				
Type of connection	connecting cable (300 mm)				
Weight	320	450	770	g	

ACCESSORIES	ARTICLE NUMBER
Thermostat	17111000000
Hygostat	17207000000
Internal enclosure fan	18110000000

For additional models, options and voltages visit www.pfannenberg.com or contact us directly.



Dimensions

mm	PRH
X	29.5
Y	45
Z	75
L	300

