

PWS 7332 L

AIR/WATER HEAT EXCHANGER 3150 W


- long passage of air
- compatible with DTS 9x41 cooling unit series
- maintenance-free
- mounting-friendly seal, no elaborate reworking of the mounting cut-out
- integrated thermostat and solenoid valve for temperature control
- integrated temperature monitoring with alarm contact




PRODUCT		PWS 7332 L		
ARTICLE NO.		12053010063	12053017063	Unit
DATA				
Rated voltage ±10 %		AC 50 60	AC 60	Hz
		230	115	V
Cooling capacity @ 200 l/h	W10/A35	3150		W
Power consumption	W10/A35	161 226	193	A
Current consumption	W10/A35	0.7 1	1.7	
Starting current	W10/A35	2.6 2	3	
Unimpeded airflow (free flow)	internal	1200		m³/h
Pre fuse T		6		A
Type of connection	electro	spring-type terminal included with plug		
	fluid	13 mm hose nozzle; other connectors on request		
Noise level according to EN ISO 3741		54		dB (A)
Weight (without packaging)		35		kg
Ambient temperature range		+1 ... +70 +34 ... +158		°C °F
Control range (adjustable)		+8 ... +50 +47 ... +122; factory setting +35 +95		
Water inlet temperature		+1 ... +35 +34 ... +95		
Permissible operating pressure		max. 10		bar
Duty cycle		100		%
Condensate management		condensate drain		
Protection system according to EN 60529	IP 55	towards the electrical enclosure if used as intended by the manufacturer		
	IP 65	on request		
Design	housing	galvanised steel electrostatically powder coated (200 °C) stainless steel on request		
	heat exchanger	copper pipe with aluminium fins stainless steel piping on request		
Colour	cover	RAL 7035 different colours available on request		
ACCESSORIES		Piece	ARTICLE NUMBER	
External condensate evaporation system		1	18314000001	
Condensate bottle		1	18314000100	

For additional models, options and voltages visit www.pfannenbergl.com or contact us directly.

Cooling capacity performance curves



Pressure loss performance curve



Dimensions

	X	Y	Z	A	B	C	D	E	F	G	H	I
mm	400	1350	190	700	315	220	350	450	510	290	350	58

Mounting holes \varnothing 8 mm and cut-out radii R20

PWS 7332 L

